

DENTAL TRIBUNE

The World's Dental Newspaper • Middle East & Africa Edition

PUBLISHED IN DUBAI

www.dental-tribune.me

May-June 2021 | No. 3, Vol. 11

ENDO TRIBUNE

Environmental sustainability in endodontics

►A1-4

LAB TRIBUNE

Women in dentistry: Meet dental technician and researcher Dr Joanane Choi

►B1-4

IMPLANT TRIBUNE

Effectively designing the aesthetic zone

►C1-4

ORTHO TRIBUNE

The future of dentistry: An inevitable shift towards a digital ecosystem

►D1-4

HYGIENE TRIBUNE

Laser assisted prophylaxis around zirconia implants

►E1-4

Transmission of SARS-CoV-2 in dental offices very unlikely, study says

By Dental Tribune International

COLUMBUS, Ohio, U.S.: Researchers worldwide investigate COVID-19, and every week, new information about the illness is discovered or confirmed. A recent study from the Ohio State University has shown yet again that a SARS-CoV-2 infection risk at the dentist's office is low, despite the tenacious misconception that patients and treatment providers are at high risk of catching COVID-19 at the dentist's office.


Dental procedures are known to produce a considerable amount of aerosol, and this leads to fears that saliva in the aerosols generated during dental treatments could make the dentist's chair a high-transmission location since SARS-CoV-2 spreads

mainly through respiratory droplets. In order to investigate whether saliva is the main source of the spray, the researchers collected samples from personnel, equipment and other surfaces reached by aerosols during a range of dental procedures.

By analysing the genetic makeup of the organisms detected in those samples, the researchers determined that dental irrigant, not saliva, was the main source of any bacteria or viruses present in the spatter and spurts from patients' mouths. Even when low levels of SARS-CoV-2 were detected in the saliva of asymptomatic patients, the aerosols generated during their procedures showed no signs of SARS-CoV-2.

"Getting your teeth cleaned does not increase your risk for COVID-19 infection any more than drinking a glass of water from the dentist's office does," said lead author Dr. Purnima Kumar, professor of periodontics at Ohio State. "These findings should help us open up our practices, make ourselves feel safe about our environment and, for patients, get their oral and dental problems treated—there is so much evidence emerging that if you have poor oral health, you are more susceptible to COVID," Kumar added.

The study, titled "Sources of SARS-CoV-2 and other microorganisms in dental aerosols," was published online on May 12, 2021, in the *Journal of Dental Research*, ahead of inclusion in an issue. **DT**



AD

#whdentalwerk
f @ in
video.wh.com

Now at
your dealer
or **wh.com**



20 YEARS
IMPLANTMED

**20 Years of
Pioneering Spirit**

Pioneering Spirit. Proven Experience.

Implantmed developed in the last 20 years from newcomer to today's smart device bestseller in the field of dental implantology and oral surgery.

W&H

implantmed

Meet A-dec's new territory manager for the Middle East



© Nick Olive

By A-dec

As part of a continued focus on supporting customers globally, A-dec are pleased to welcome Nick Olive to the role of Territory Manager for the Middle East. Nick moves from A-dec's UK business, where he has been helping UK dentists to find ergonomic and reliable equipment for their practices since 2014.

Nick is currently based in the UK but plans to move to Dubai in the near future to work closely with the valued distribution partners A-dec has in the region. He will also be on hand for product demonstrations, trade shows and to assist A-dec customers. Please join us in congratulating Nick on his new role and reach out to him if you have any questions regarding A-dec equipment. [DT](#)



If you would like to contact Nick, you can reach him on +447824 021839 or at nick.olive@a-dec.com

IMPRINT

PUBLISHER AND CHIEF EXECUTIVE OFFICER

Torsten R. OEMUS

CHIEF CONTENT OFFICER

Claudia DUSCHEK

DENTAL TRIBUNE INTERNATIONAL

Holbeinstr. 29, 04229 Leipzig, Germany

Tel.: +49 341 48 474 302

Fax: +49 341 48 474 173

www.dental-tribune.com

General requests:

info@dental-tribune.com

Sales requests:

mediasales@dental-tribune.com

DENTAL TRIBUNE MEA

EDITION EDITORIAL BOARD

Dr. Aisha SULTAN ALSUWAIDI, UAE

Prof. Paul TIPTON, UK

Prof. Khaled BALTO, KSA

Dr. Ninette BANDAY, UAE

Dr. Nabeel HUMOOD ALSABEEHA, UAE

Dr. Naif Almosa, KSA

Dr. Mohammad AL-OBAIDA, KSA

Dr. Meshari F. ALOTAIBI, KSA

Dr. Jasim M. AL-SAEEDI, Oman

Dr. Mohammed AL-DARWISH, Qatar

Dr. Dobrina MOLLOVA, UAE

Dr. Ahmed KAZI, UAE

Dr. Munir SILWADI, UAE

Dr. Khaled ABOUSEADA, KSA

Dr. Rabih ABI NADER, UAE

Dr. Ehab RASHED, UAE

Dr. Mohd Dashti, Kuwait

Aiham FARRAH, CDT, UAE

Retty M. MATTHEW, UAE

PARTNERS

Saudi Dental Society

Saudi Ortho Society

Lebanese Dental Association

Lebanese Orthodontic Society

Qatar Dental Society

Oman Dental Society

Kuwait Dental Association

International Federation of Dental

Hygienist

British Academy of Restorative Dentistry

British Academy of Dental Implantology

AALZ - Aachen Dental Laser Center

Singapore Dental Association

Saudi Dental Hygienist Society

DIRECTOR OF mCME

Dr. Dobrina MOLLOVA

mollova@dental-tribune.me

Tel.: +971 50 42 43072

DIRECTOR

Tzvetan DEYANOV

deyanov@dental-tribune.me

Tel.: +971 55 11 28 581

EDITING & DESIGN

Kinga MOLLOV

kromik@dental-tribune.me

Tel.: +971 56 23 70 721

PRINTING HOUSE & DISTRIBUTION

Al Nisr Printing

P. O. Box 6519, Dubai, UAE

800 4585/04-4067170

Material from Dental Tribune International GmbH that has been reprinted or translated and reprinted in this issue is copyrighted by Dental Tribune International GmbH. Such material must be published with the permission of Dental Tribune International GmbH. Dental Tribune is a trademark of Dental Tribune International GmbH.

All rights reserved. © 2021 Dental Tribune International GmbH. Reproduction in any manner in any language, in whole or in part, without the prior written permission of Dental Tribune International GmbH is expressly prohibited.

Dental Tribune International GmbH makes every effort to report clinical information and manufacturers' product news accurately but cannot assume responsibility for the validity of product claims or for typographical errors. The publisher also does not assume responsibility for product names, claims or statements made by advertisers. Opinions expressed by authors are their own and may not reflect those of Dental Tribune International GmbH.

AD

formlabs  | dental

Digital Transformation Made Accessible

An advanced desktop 3D printing ecosystem, optimized for dental workflows from a trusted leader in additive manufacturing.



North American Sales Inquiries

dental@formlabs.com

+1 (617) 702 8476

dental.formlabs.com

Europe Sales Inquiries

dental@formlabs.com

+49 30 8878 9870

dental.formlabs.com/eu

International Sales Inquiries

Find a reseller in your region:

formlabs.com/find-a-reseller

CHALLENGE ACCEPTED.

Nobody thought a bulk fill flowable was possible.
Until we invented Surefil® SDR flow+ Material. Today, we
redefine restorative materials again with Surefil one™ Restorative,
transforming how dentists manage challenging clinical situations
where isolation is difficult or when patient compliance is an issue.

- **Self-adhesive**—no separate adhesive step needed
- **Unlimited depth of cure**—no layering of composite materials, making it faster than a traditional composite restoration, **especially in compromised cases.**

Surefil one™ Restorative. Progress where you need it most.
For more information visit DentsplySirona.com

Surefil one™
Self-Adhesive Composite Hybrid

How PIEZOSURGERY has redefined bone surgery

20 years of PIEZOSURGERY technology

By mectron s.p.a.

Twenty years ago, the International Dental Show (IDS) saw the premier of the PIEZOSURGERY unit, a first for piezoelectric bone surgery. Since then, mectron has not only succeeded in revolutionising clinical reality with PIEZOSURGERY, but also benefitted practitioners and patients worldwide with two decades of ease of use and minimal invasiveness.

"When I started developing piezoelectric bone surgery more than 20 years ago, I never expected that Piezosurgery would redefine all bone surgery," says Prof. Tomaso Vercellotti, the inventor of PIEZOSURGERY, today, 20 years after the first system was launched.

Yet the success story of the original PIEZOSURGERY method was already underway in 1997, when the peri-

odontist Vercellotti, in partnership with the company mectron, began working on the idea of ultrasonic bone surgery. Even then it was clear to them: an essential success factor for oral surgical treatment is reducing its invasiveness to a minimum, ensuring that the surrounding soft tissue is spared, therefore enabling rapid healing. Vercellotti and mectron saw a solution for this in the use of modulated ultrasonic vibra-



AD

THE EVOLUTION OF PROPHYLAXIS COMBI touch

AIR-POLISHING AND ULTRASOUND IN ONE UNIT

- easy switch from supra to subgingival air-polishing by a simple click
- subgingival perio air-polishing tip – flexible, soft and anatomically adjustable to the periodontal pocket
- more than 40 inserts for scaling, perio, endo and prosthetics
- SOFT MODE: the ultra-gentle scaling for sensitive patients



→ www.mectron.com



mectron
medical technology

tions. Shortly afterwards, mectron succeeded in building the first prototype and carrying out the first extraction treatments.

PIEZOSURGERY: A new paradigm in bone surgery

In 2001 the time had come: The world's first PIEZOSURGERY device was presented at IDS. In 2005, the first implant bed preparation using PIEZOSURGERY was successfully completed. Vercellotti: "2005 was also the year in which a grand master of periodontology from Harvard University defined PIEZOSURGERY as a new paradigm. Making us very happy, of course." And indeed, piezoelectric bone surgery became a clinical reality worldwide over the following years. This success is based not only on the exceptional intraoperative control PIEZOSURGERY offers its users, but also the reduction in the surgical trauma to the surrounding tissue, enabling faster healing than after more invasive cutting surgical procedures.

In 2011, the 4th generation of PIEZOSURGERY equipment was launched. Other groundbreaking milestones include in 2015, when the world's narrowest osteotomy instrument, OT12S, was introduced. With a width of only 0.25 mm, it is suitable for all osteotomy techniques where standard bone saws have access difficulties. In 2019, the REX PiezoImplant was launched on the market as the first implant with a minimally invasive implant bed prepared exclusively with PIEZOSURGERY. The innovative REX PiezoImplant wedge implants are suitable for use in the narrow ridge of the jawbone. This is because their unusual shape means that the bone does not have to be augmented before the implant is placed.

30,000 customers in over 80 countries have already been won over

Today, more than 250 scientific and clinical studies have proven the positive effects of using the PIEZOSURGERY method. The more than 90 different instruments for the PIEZOSURGERY equipment are exclusively produced in Italy and distributed worldwide in more than 80 countries. More than 30,000 customers have so far been convinced of the advantages of piezoelectric bone surgery. Vercellotti: "The commitment of all those involved in improving PIEZOSURGERY year on year has been rewarded with the confidence of an extraordinary number of surgeons and, above all, with the satisfaction of the patients treated."

DT



Science.
Applied to Life.™



3M™ Imprint™ 4 VPS Impression Material Stress less over everyday impressions.

Say “YES” to the VPS impression material with the shortest intra-oral setting time. Move through your day with speed, control and precision.

Speed.

Reduced chair time and stress for patients—Imprint 4 material has the shortest intra-oral setting time among leading VPS fast-setting impression materials.

Control.

Long working time for you. Due to the unique chemistry, the setting time doesn't start until the END of the working time. That means you'll have a sufficient amount of time to load and seat the tray—no stressful race against the clock.

Precision.

Super hydrophilicity. Imprint 4 material is super-hydrophilic, displacing moisture right from the start in the unset state—which helps prevent detail-disrupting voids.



To learn more how our NEW Imprint 4 VPS Impression Material can Impress you with the results simply scan the QR Code and we'll be in touch with you!

Email: 3moralcaresa@mmm.com

EyeSpecial CIV Smart Digital Dental Camera



By Shofu

Shofu's Gen 4 smart digital dental camera is developed to shoot fast, predictable and consistent clinical photographs for everyday dentistry.

Equipped with state-of-the-art digital technology, this foolproof, ultra-light and compact dental camera is designed exclusively for your dental team to shoot clear, consistent clinical photos in true-colour each time.

No prior photography knowledge required, as it comes with one-touch operation and an intuitive menu to guide the user to select from any of the nine pre-set dental shooting modes. Easy to wipe clean and disinfect in between patients, it complies with stringent infection control protocols at the dental operatory.

This user-friendly camera is the ideal choice for your practice as it meets user-specific needs ranging from routine intra-oral photography, diagnosis and treatment planning, orthodontic evaluation, dental lab and specialist collaboration, patient communication and education to legal documentation and insurance verification.

EyeSpecial features

- Nine pre-set dental shooting modes
- Compact, Ultra-light & Easy to hold with one hand
- Fast auto-focus with built-in anti-shake with image stabilization and anti-reflection features
- Cutting edge Flashmatic System for True-colour reproduction with blackout of ambient light

- Water, chemical and scratch resistant to prevent cross contamination
- Brilliant display with fast & Intuitive menu navigation
- Video function
- Micro HDMI connector
- QR code features
- Trigger Flash Mode for portrait photography
- Optional attachable cross polarizer 

For further information, please contact:

SHOFU DENTAL ASIA-PACIFIC PTE LTD
10 Science Park Road, #03-12 The Alpha
Singapore Science Park II
Singapore 117684
Tel: (65) 6377 2722
Fax: (65) 6377 1121
E-mail: mailbx@shofu.com.sg
Web: www.shofu.com.sg

Interview: “Attempting to make my own shield seemed like a productive use of time”

By Iveta Ramonaite, Dental Tribune International

The pandemic has caused professional and private challenges. However, some people managed to use this downtime to stimulate their creativity and to test their entrepreneurial skills. One of these people is Dr. Scott Yamaoka, who devoted his time and energy to creating a face shield that would protect his dental team and patients from SARS-CoV-2 infection in the workplace. In this interview, he and his son, Zach Yamaoka, tell Dental Tribune International how they turned their idea into a product—the next generation optical face shield that allows dentists to comfortably fit magnification loupes with fiber optic lighting.

First of all, congratulations on your invention! Could you start by telling our readers a bit about your creation and what led you to developing it at home in your garage, during the pandemic?

Dr. Scott Yamaoka: As the pandemic set in and dental offices shut down, I began thinking about how we could get back to work safely. It became clear that, moving forward, face shields would be necessary to protect our dental team and patients. Images of hospital workers helping COVID-19 patients were circulating in the news, and that really drove this message home.

At the outset of the pandemic, it was nearly impossible to get one of these shields, which were sold out everywhere. And even if you could somehow get one, I realized that the shields that were made of foam and plastic film and used by hospital workers would be ineffective in the dental environment, in which dental professionals require clarity, the accommodation of magnification loupes and fiber optic lighting. The only other options available were construction shields from the hard-



Vancouver-based periodontist Dr. Scott Yamaoka (left) and his son Zach Yamaoka, design engineer at Dyson.

ware store. But even those had sold out, and again, would not accommodate magnification and lighting.

Attempting to make my own shield seemed like a productive use of time and mental energy during the shut-down and gave me solace in that I could control a small part of my destiny and the outcome of the pandemic.

It is not easy to create a face shield that not only is pleasing to the eye but also has a protective function. Could you take our readers through the creation process and talk about some of the materials you used?

Dr. Scott Yamaoka: Creating the prototype was a matter of searching for available products that I could use to construct the basic components of the face shield: a head harness, a plastic attachment system and the plastic itself.

While looking at industrial shields for welding and researching the construction industry, I had the idea to use a safety construction helmet. We had one at home. The benefits of the secure head harness provided the foundation, and the brim allowed space for optics and lights. Removing the top part of the helmet with a Dremel reduced the weight and also allowed the plastic material to adapt to the rim of the brim to secure the magnets.

Using magnets meant that dentists could efficiently change the sheets of visor plastic in between patient visits and replace them when they became damaged or scratched. Seeing magnets on our fridge for holding paper notes gave me the idea that they could be used to secure the plastic, provided they were strong enough to hold it. We have used rare-earth magnets to surgically move teeth, and similar products were available at the hardware store.

Visor plastic was not available anywhere at the time, so I thought that we could use acetate plastic from the overhead projectors we once used when I was in grade school. Fortunately, they were still on sale, but their clarity was not ideal. The plastic we are using now is imported from the U.K. and incorporates the latest advances in clarity, including proprietary nanosurface technology. One of the comments we receive the most is that people forget that they are wearing the shield!

Zach Yamaoka: As the shield developed, we incorporated more Aesthetic aspects. However, the function of the face shield has always been important, since things are only beautiful if they work. The thinness of the rim on the final product is the result of a desire to reduce weight. The square shape reduces glare from ambient light. The appearance of each component on the shield is tied to a functional aspect.

The face shield we see now required 58 prototypes. What did you learn in the process, and when did you know that the product was ready to be sold on the market?

Zach Yamaoka: The story of the Loupe Shield engineering is the story of three discoveries made while making 58 prototypes.

The first one was that dentists really liked the full head harness. The users of the safety helmet prototype commented that, compared with their current face shield with an elastic band, the full safety harness was more comfortable, secure during long operations and caused fewer headaches. When analyzing this feedback, we realized that the key is the top strap. It supports the weight of the face shield and alleviates pressure on the sides of the head.

The second discovery was that a square rim has better optical properties. Searching online, I came upon an image of a face shield where the visor was gently curved in the field of view. We wondered what would happen if we extended that principle further, so we adjusted the shape of our rim from a semicircle (curved at the front) to a square (flat at the front). From testing, we realized that this reduced optical distortion and minimized glare from ambient light. As optical clarity is paramount to dental professionals, we thought this would be a great feature.

The third discovery was of an optical plastic technology initially developed for iPhone screen protectors. It turns out that the functional requirements of screen protectors, which are ultraclear and scratch-resistant, are similar to those of dental face shields. Combining this optical plastic with our square rim has resulted in a face shield that is virtually invisible and incredibly durable.

EyeSpecial C-IV

SMART DIGITAL CAMERA

Designed Exclusively for Dentistry



Everyone in your Dental Team can Shoot!

- Incredibly Compact & Light
- Insanely Easy & Accurate
- Amazingly Intuitive & Fast
- Perfect Picture Everytime



For more information, please contact your nearest SHOFU dealer Today!



SHOFU DENTAL ASIA-PACIFIC PTE. LTD.
www.shofu.com.sg



Page 6

The next-generation Loupe Shield available today incorporates these three discoveries. It features a fully adjustable head harness with a top strap, a square rim with a flat front, and a visor that was coated using this optical plastic technology.

It's hard to know when a product is ready for market. As a designer, the tendency is to continue to improve it, but this cannot go on forever; at some point you reach a local optimum. After completing the 58th prototype, we 3D-printed ten shields and sent them to dentists in the U.S., Canada, the U.K. and Germany. Eight of the dentists loved it. Common startup wisdom is that, if even one customer loves your product, it's time to go to market, so that is what we did.

Dr. Yamaoka, how did collaborating with your son, an engineer, help achieve the final result?

Dr. Scott Yamaoka: Being able to express the clinical needs for shield protection and functionality to a design engineer whose training is to take a concept and bring it into reality has been invaluable. Zach was able to take a complicated prototype and simplify its design while addressing the key needs for clinical practice.

Securing appropriate PPE has been quite challenging for many dental professionals in the past year. Why should dental teams be excited about this invention, and how will it improve their workflow?

Dr. Scott Yamaoka: Using a face shield that had poor clarity, was frequently fogged and felt uncomfortable slowed down my work. Zach and I designed the Ambience face shield to tick off all the boxes of what I would want a face shield to be. When using it, I can achieve my pre-COVID-19 level of efficiency, with the added benefit of protection. Owing to its optical clarity, it does not affect the patient experience and interaction.

I sometimes forget I am wearing it. Eye strain and neck issues have also improved for me, which is a benefit I expect others will experience as well.

Having the shield gives me the peace of mind to focus on the surgery and

the patient. The benefits can be seen after surgery when the plastic face shield is covered with bio-burden on the outside. Wearing the shield is a seamless minor inconvenience, as I am now much more aware of the ramifications of splatter on my face and loupes. This face shield has become an integral part of my practice.

Should dental professionals keep an eye out for new products?

Dr. Scott Yamaoka: The Loupe Shield is fantastic at keeping splatter and droplets off the clinician's face. It does this without sacrificing comfort or clarity. One shortcoming of face shields, in general, is that, alone, they do not provide sufficient protection against aerosol. The clinician should still wear a respirator or mask. Some face shield products

completely seal around the head to provide aerosol filtration. However, they are overly complex, hard to clean, don't fit loupes and are pricey.

As more data indicates the importance of aerosol as a mode of transmission, the desire for face shields that can protect from both splatter and aerosol will likely increase. For now, the Loupe Shield with an N95 respirator is perfect for a clinician working in a high-concentration aerosol environment. In the future, developing a Loupe Shield that offers complete protection from both splatter and aerosol would be a natural progression.

For more information, please see <https://ambienceppe.com/>. ^{1,2,3}

Matter, technology, science The origin of Zhermack solutions



By Zhermack S.p.A.

From the seaweed of Northern seas to the most widely-used alginates in the world of dentistry: a pathway that follows the specific values that have made Zhermack popular with sector professionals.

Creativity, accessibility, substance

and dynamism to develop solutions able to perfectly satisfy user needs.

Essential for clinical practice

Alginates have been used in clinical practice for over 50 years. These materials of plant origin, extracted from seaweed, are particularly popular because they are well tolerated by patients, easy to use and elastic.^{1,2,3}

These characteristics make alginates suitable for use in most types of dentistry^{4,5}, including for preliminary impressions.

A complete range, for all applications

All Zhermack alginates undergo rigorous testing, both during production processes and in the choice of

raw materials, in order to guarantee compliance with the most stringent quality standards.

A vast range of alginates is available, with specific characteristics that cater for all the diverse demands of daily clinical practice. All products can be disinfected, as well as being gluten- and lactose-free, demonstrating the great attention that Zhermack dedicates to both the work of practitioners and the health of patients.

From tradition to the future: Zhermack embraces technological innovation and the new frontiers of digital work-flows with the scannability of Hydrogum 5, its top-of-the-range product ⁶.

References

1. Gherlone E. L'impronta in protesi dentaria. 3rd edition. Edra; 2017
2. Cervino G, Fiorillo L, Herford AS, et al. Alginate Materials and Dental Impression Technique: A Current State

of the Art and Application to Dental Practice. Mar Drugs. 2018;17(1):18. Published 2018 Dec 29. doi:10.3390/

md17010018

3. Thirunavakarasu R, Nittla P. P, Alginate impression material - a review, Drug invention today. 2018; 10(4): 3556-3561. ISSN: 0975-7619

4. Bortolini S, Consolo U, Rossi R. L'impronta in implantoprotesi. 2008; 25

5. Bortolini S, Consolo U, Rossi R. L'impronta in implantoprotesi. 2008; 18

For more information, contact

Zhermack S.p.A.
Via Bovazecchino, 100
45021 Badia Polesine (RO) Italy
Tel. +39 0425 597712
Fax. +39 0425 53596
Web. www.zhermack.com

AD

PROMEDICA

Highest quality made in Germany

Medifil IX forte LC
Application Cap

Glass ionomer filling material

- Setting time is individually adjustable by light-curing
- No need to condition the dental hard tissue
- Immediately packable after placement in the cavity
- Does not stick to the instrument and is easy to model
- No varnish required - fill, polymerise and finish

Success CD

Temporary crown & bridge material

- Less than 1 min. setting time in the mouth
- Auto-mixing, homogenous and bubble-free paste
- Excellent transverse and compressive strength
- Perfect long-term aesthetics: brilliant enamel-like gloss and high colour stability
- Withstands strong functional loads

Composan LCM

Light-curing micro-hybrid composite

- Universal for all cavity classes
- Sticks to the cavity not to the instrument
- Perfect aesthetics
- High translucency and perfect colour adaption
- Polishable to a high gloss
- Superior physical properties
- Packable consistency (also available as Composan LCM flow)

Visit www.promedica.de to see all our products

PROMEDICA

Dental Material GmbH
24537 Neumünster / Germany
Tel. +49 43 21 / 5 41 73
Fax +49 43 21 / 5 19 08
eMail info@promedica.de
Internet www.promedica.de



extraPro

HIGH-TECH,
HIGH-PERFORMANCE
SOLUTIONS

specialPro

SOLUTIONS FOR SPECIFIC
APPLICATIONS

multiPro

VERSATILE SOLUTIONS

easyPro

ESSENTIAL SOLUTIONS

Rev. 2020-07

alginates

Matter, technology, science.
The origin of Zhermack solutions.

Zhermack alginates satisfy the **most stringent quality** standards in terms of both the raw materials used and the solutions proposed.

A **vast range** with distinctive characteristics to satisfy the diverse demands of daily clinical practice.

Chromatic and non-chromatic solutions with different setting times (normal, fast and extra-fast), surface detail reproduction down to 5 microns and dimensional stability for up to 5 days.

First, the impression

www.zhermack.com

Some products may not be available in all countries.
For further information on product availability, please contact your local representative.

Gluten
Lactose
FREE



Zhermack 
Dental